

**ON** → **ON**

**CLEAR OFF** → **OFF**

2 sec

**ON**

8.532 m

**ON 2 sec**

min.

max.

1x

2 sec

2x

2 sec

3x

4x

5x

6x



0.625 m

0.625 m



0.625 m



Adjust delay of automatic release



History (1-20)



$\lambda=635\text{nm}$   $P_{\text{av}}=0.95\text{mW}$   $t_p>400\text{ps}$   
IEC 60825-1:2014

[www.makita.com](http://www.makita.com)



LCA795832a




2 sec



2 sec




2 sec



**Makita**

**LD080P**

## QUICKSTART



- 1 Display
- 2 On / Measure
- 3 Add
- 4 Area / Volume / Pythagoras / Stake out
- 5 Clear / Off
- 6 Memory
- 7 Subtract
- 8 Timer
- 9 Measuring reference / Units